

GT-D34

Wascator Automatic Shrinkage Tester



Application

Wascator Automatic Washing Shrinkage Tester. Accelerated washing apparatus for knitted and woven fabrics to assess shrinkage in accordance with international test methods. Also used for assessing fabric stability, color fastness, finish durability, spirality and pilling to washing.

Feature

- ✧ MCU program controller, build-in ten sets of washing program that ISO required, and operator program capability.
- ✧ No need to fix to ground with foot screw, operating stably;
- ✧ Soft link between rotating cage and rack, low vibration and noise;
- ✧ Variable frequency motor, switch smoothly between high speed and low speed, low temperature increment of motor.
- ✧ Blue fluorescence LCD display, test state dynamic icon shows, easier to catch the eye and operation convenience.
- ✧ Non-touch capacitance water level meter to measure water level accuracy and reliable

Key Specification

Model	GT-D34		
Washing model	front-loading, horizontal tumbling-box type		
Diameter oftumbling-box	515+/-5mm		
Depth oftumbling-box	335+/-5mm		
Interval between inner andouter tumbling-box	28+/-1mm		
Number of lifter	3		
Height of lifter	50+/-5mm		
Rotatingmethod			
Normal model:	clockwise rotating	12+/-0.1s,	pause 3+/-0.1s,
	anticlockwise rotating	12+/-0.1s,	pause 3+/-0.1s
Soft model:	clockwise rotating	3+/-0.1s,	pause 12+/-0.1s,
	anticlockwise rotating	3+/-0.1s,	pause 12+/-0.1s
Rotation speed	Washing	52r/min	
	Spin	(500+/-20)r/min	
Fill water time	< 2min(water in high level 13cm)		
Drainage duration	< 1min(water in high level 13cm)		
Heating power	5.4+/-2%KW		
Load weight	5kg		
Power supply	Ac220V 50Hz 5400W		
Instrument size	990x980x1450mm(LxWxH)		
Weight	280kg		
Standards	BS/ISO 6330/5077 , AATCC 135		

GESTER INTERNATIONAL CO.,LTD

12-112 ShuiAnJiaRi , Jiang BinBei Road, FengZe Region, Quanzhou of Fujian. 362000. China

TEL: 86 0595-22515230

FAX: 86 0595 22515221

E-mail: gester@gester-instruments.com

Web: www.gester-instruments.com